



EQ 型磁芯
EQ CORES




規格 (Type)	尺寸(Unit : mm)							圖形	磁芯參數				單重 (g/set)	Al-value (nH/N ²)											
	A	B	C	D1	D ₂	E	F		C1 (mm ⁻¹)	Le (mm)	Ae (mm ²)	Ve (mm ³)		KP40	KP44	KP44L	KP50	KP95	KP96	KP97	KA50	KA70	KA100	KA120	
EQ18/6.3	18.00±0.35	6.30±0.20	9.70±0.20	15.60±0.30	13.50min	6.20±0.15	3.20±0.30	Fig.1	0.682	21.0	30.8	646.80	3.50				2400	2290	2900	2770	2770				
EQ18/08	18.00±0.35	8.00±0.20	9.70±0.20	15.60±0.30	13.50min	6.20±0.15	4.90±0.30	Fig.1	0.859	26.1	30.4	793.44	4												
EQ20/9.8B	20.00±0.35	9.80±0.20	14.00±0.30	18.00±0.35	12.86±0.35	8.80±0.20	5.80±0.30	Fig.2	0.513	29.3	57.1	1673.03	8.60				4200	3940	4500	4260	4260				
EQ20/9.9	20.00±0.35	9.90±0.20	14.00±0.30	18.00±0.35	12.86±0.35	8.80±0.20	5.70±0.30	Fig.2	0.501	29.3	58.5	1714.05	8.70				4200	3940	5900	5500	5500				
EQ20/10A	20.00±0.35	10.00±0.20	14.00±0.30	18.00±0.35	12.86±0.35	8.80±0.20	5.90±0.30	Fig.2	0.512	29.6	57.8	1710.88	8.80				4100	3850	4500	4260	4260				
EQ20/10.4	20.00±0.35	10.40±0.20	14.00±0.30	18.00±0.35	12.86±0.35	8.80±0.20	6.00±0.30	Fig.2	0.461	27.5	59.7	1641.75	9.30				4070	3850	4890	4640	4640				
EQ20/10.7	20.00±0.35	10.70±0.20	14.00±0.30	18.00±0.35	12.86±0.35	8.80±0.20	6.50±0.20	Fig.2	0.529	30.9	58.4	1804.56	9.20				3700	3490	5090	4780	4780				
EQ20/11.6	20.00±0.35	11.60±0.20	14.00±0.30	18.00±0.35	12.86±0.35	8.80±0.20	7.40±0.30	Fig.2	0.558	32.6	58.4	1903.84	9.75				3750	3530	4300	4060	4060				
EQ20/11.8	20.00±0.35	11.80±0.20	14.00±0.30	18.00±0.35	12.86±0.35	8.80±0.20	7.40±0.30	Fig.2	0.551	32.8	59.5	1951.60	10.30				3800	3570	4750	4470	4470				
EQ20/12.2	20.00±0.35	12.20±0.30	14.00±0.30	18.00±0.35	12.86±0.35	8.80±0.20	7.80±0.30	Fig.2	0.565	33.6	59.5	1999.20	10.50				3200	3030	4300	4060	4060				
EQ20/12.2A	20.00±0.35	12.20±0.20	14.00±0.30	18.00±0.35	12.86±0.35	8.80±0.20	8.00±0.30	Fig.2	0.570	33.9	59.4	2011.88	10.10				3600	3390	4200	3970	3970				
EQ20/12.6	20.00±0.35	12.60±0.20	14.00±0.30	18.00±0.35	12.86±0.35	8.80±0.20	8.20±0.30	Fig.2	0.579	34.4	59.4	2043.36	10.70				3150	2990	4300	4060	4060				
EQ20/15	20.00±0.35	15.00±0.20	14.00±0.30	18.00±0.35	12.86±0.35	8.80±0.20	10.60±0.30	Fig.2	0.662	39.2	59.2	2320.64	11.76				3200	3000	3960	3730	3730				
EQ20/15.4	20.00±0.35	15.40±0.20	14.00±0.30	18.00±0.35	12.86±0.35	8.80±0.20	11.00±0.30	Fig.2	0.676	40.0	59.2	2368.00	12.00				3100	2930	4100	3860	3860				
EQ20/17.8	20.00±0.35	17.80±0.20	14.00±0.30	18.00±0.35	12.86±0.35	8.80±0.20	13.40±0.30	Fig.2	0.759	44.8	59.0	2643.20	13.30				3000	2810	3600	3380	3380				
EQ25/8.2A	25.00±0.40	8.20±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	3.40±0.30	Fig.1	0.316	28.6	90.6	2591.16	13.60				6800	6380	7300	6910	6910				
EQ25/9.1	25.00±0.40	9.10±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	3.5±0.30	Fig.1	0.261	25.8	99.0	2554.20	15.20				6200	5910	8400	7980	7980				
EQ25/10	25.00±0.40	9.80±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	4.10±0.30	Fig.1	0.308	30.8	100	3080.00	15.80	5800	6000	6000	5680	7500	7100	7100					
EQ25/10A	25.00±0.40	10.10±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	4.40±0.30	Fig.1	0.314	31.4	100	3140.00	16.10		6000	6000	5680	7500	7100	7100					
EQ25/10B	25.00±0.40	10.00±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	5.20±0.30	Fig.1	0.352	32.1	91.3	2930.73	15.30				5700	5370	6800	6430	6430				
EQ25/10C	25.00±0.40	10.00±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	5.40±0.30	Fig.1	0.362	32.3	89.2	2881.16	15.00		5500	5500	5190	6600	6240	6240					
EQ25/10.1	25.00±0.40	10.10±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	5.10±0.30	Fig.1	0.345	32.2	93.4	3007.48	15.60				6000	5650	7000	6610	6610				
EQ25/10.2A	25.00±0.40	10.20±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	5.40±0.30	Fig.1	0.357	32.6	91.4	2979.64	15.40				5580	5260	6800	6420	6420				
EQ25/10.3	25.00±0.40	10.30±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	4.60±0.30	Fig.1	0.318	31.8	100	3180.00	16.80	5560	5800	5800	5490	7250	6870	6870					
EQ25/10.8A	25.00±0.40	10.80±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	6.00±0.30	Fig.1	0.377	34.6	91.7	3172.82	16.10				5490	5170	6600	6220	6220				
EQ25/11.2	25.00±0.40	11.20±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	6.40±0.30	Fig.1	0.377	34.6	91.7	3172.82	16.20		5500	5500	5170	6600	6220	6220					
EQ25/11.2Q	25.00±0.40	11.20±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	6.20±0.30	Fig.1	0.366	34.3	93.7	3213.91	16.54				5800	5460	7200	6760	6760				
EQ25/11.6A	25.00±0.40	11.60±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	6.90±0.30	Fig.1	0.389	35.4	90.9	3217.86	16.70				5500	5170	6900	6480	6480				

EQ 型磁芯
EQ CORES



規格 (Type)	尺寸(Unit : mm)							圖形	磁芯參數				單重 (g/set)	Al-value (nH/N ²)											
	A	B	C	D1	D ₂	E	F		C1 (mm ⁻¹)	Le (mm)	Ae (mm ²)	Ve (mm ³)		KP40	KP44	KP44L	KP50	KP95	KP96	KP97	KA50	KA70	KA100	KA120	
EQ25/11.7A	25.00±0.40	11.70±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	7.10±0.30	Fig.1	0.397	35.7	89.9	3209.43	16.60			5200	4900	7300	6820	6820					
EQ25/11.7	25.00±0.40	11.70±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	6.10±0.30	Fig.1	0.349	34.7	99.3	3445.71	17.80			6100	5730	7550	7100	7100					
EQ25/12	25.00±0.40	12.00±0.25	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	6.30±0.30	Fig.1	0.352	35.2	100	3520.00	18.20			5800	5500	7100	6700	6700					
EQ25/12A	25.00±0.40	12.00±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	7.20±0.30	Fig.1	0.395	36.1	91.5	3303.15	17.20			5400	5070	6400	6030	6030					
EQ25/12.4	25.00±0.40	12.40±0.25	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	6.70±0.30	Fig.1	0.359	35.9	100	3590.00	18.70		5310	5310	5020	7300	6870	6870					
EQ25/13	25.00±0.40	13.00±0.25	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	7.30±0.30	Fig.1	0.372	37.2	100.0	3720.00	19.20			5700	5350	7000	6610	6610					
EQ25/13A	25.00±0.40	13.00±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	8.20±0.30	Fig.1	0.413	38.1	92.3	3516.63	18.15			5480	5130	6900	6440	6440					
EQ25/14	25.00±0.40	14.00±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	8.30±0.30	Fig.1	0.391	39.1	99.9	3906.09	21.00			5600	5250	6700	6300	6300					
EQ25/14A	25.00±0.40	14.00±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	9.20±0.30	Fig.1	0.434	40.1	92.5	3709.25	19.03			4780	4500	6100	5730	5730					
EQ25/14.9A	25.00±0.40	14.90±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	10.30±0.30	Fig.1	0.463	42.1	91.0	3831.10	19.60			4800	4500	6000	5600	5600					
EQ25/15.5A	25.00±0.40	15.50±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	10.70±0.30	Fig.1	0.464	43.1	92.9	4003.99	20.50			5400	5020	7400	6830	6830					
EQ25/16	25.00±0.40	16.00±0.20	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	10.30±0.30	Fig.1	0.433	43.2	99.7	4307.04	22.05		5000	5000	4690	6200	5820	5820					
EQ25/18.6	25.00±0.40	18.60±0.25	18.00±0.30	22.00±0.40	14.50min	11.00±0.20	12.90±0.30	Fig.1	0.485	48.3	99.5	4805.85	24.42			4700	4400	5900	5530	5530					
EQ30/10	30.00±0.50	10.00±0.30	20.00±0.30	26.00±0.40	----	11.00±0.20	4.40±0.30	Fig.2	0.323	35.2	109	3836.80	21.00	6600	6880	6880	6450	8600	8060	8060					
EQ30/11	30.00±0.50	11.00±0.30	20.00±0.30	26.00±0.40	----	11.00±0.20	5.40±0.40	Fig.2	0.338	37.2	110	4092.00	22.10			6900	6450	7600	7150	7150					
EQ30/11.7	30.00±0.50	11.70±0.30	20.00±0.30	26.00±0.50	----	11.00±0.30	6.30±0.30	Fig.2	0.359	38.8	108	4190.40	22.50			6480	6050	7200	6780	6780					
EQ30/12	30.00±0.50	12.00±0.30	20.00±0.30	26.00±0.40	----	11.00±0.20	6.60±0.40	Fig.2	0.365	39.4	108	4255.20	22.80			6280	5870	7160	6730	6730					
EQ30/15.5B	30.00±0.50	15.50±0.30	20.30±0.30	25.40±0.40	----	13.30±0.20	9.90±0.30	Fig.2	0.337	43.8	130	5694.00	30.20			7300	6800	9300	8640	8640					
EQ30/16	30.00±0.50	16.00±0.30	20.00±0.30	26.00±0.40	----	11.00±0.20	10.60±0.40	Fig.2	0.396	43.2	109	4708.80	27.00	5700	5900	5900	5510	6800	6380	6380					
EQ30/16B	30.00±0.50	16.00±0.30	20.30±0.30	25.40±0.40	----	13.30±0.20	10.40±0.30	Fig.2	0.350	45.5	130	5915.00	30.90			6300	5910	7850	7360	7360					
EQ30/18.8	30.00±0.50	18.80±0.30	20.00±0.30	26.00±0.40	----	11.00±0.20	13.20±0.40	Fig.2	0.443	48.7	110	5357.00	30.70	4900		5060	4740	6350	5950	5950					
EQ30/19	30.00±0.50	18.80±0.30	20.30±0.30	25.40±0.40	----	13.30±0.20	13.20±0.30	Fig.2	0.345	47.2	137	6466.40	35.00	6250	6450	6450	6050	8080	7570	7570					
EQ30/22B	30.00±0.50	22.00±0.30	20.30±0.30	25.40±0.40	----	13.30±0.20	16.40±0.30	Fig.2	0.434	57.3	132	7563.60	39.28			5370	5000	6800	6360	6360					
EQ33/12.6	33.00±0.50	12.60±0.20	24.00±0.30	29.00±0.40	24.30+0.50-0.30	13.85±0.20	6.60±0.30	Fig.1	0.295	43.7	148	6467.60	32.10			7800	7300	9870	9220	9220					
EQ33/13.2	33.00±0.50	13.20±0.20	24.00±0.30	29.00±0.40	24.30+0.50-0.30	13.85±0.20	7.20±0.30	Fig.1	0.303	44.9	148	6645.20	33.40			7600	7100	9580	8950	8950					
EQ33/14.2	33.00±0.50	14.20±0.20	24.00±0.30	29.00±0.40	24.30+0.50-0.30	13.85±0.20	8.20±0.30	Fig.1	0.317	46.9	148	6941.20	34.85			6660	6260	8800	8240	8240					
EQ33/19	33.00±0.50	19.00±0.20	24.00±0.30	29.00±0.40	24.30+0.50-0.30	13.85±0.20	13.00±0.30	Fig.1	0.379	56.5	149	8418.50	41.25			5500	5170	7600	7100	7100					
EQ39/27	39.80±0.50	27.00±0.30	32.50±0.4	35.4 min	24.4 min	19.00±0.25	16.80±0.30	Fig.1	0.200	61.8	309	19116.41	108.56	7500	9000	9000	6500	12000	12000	10000					

EQ 型磁芯
EQ CORES



規格 (Type)	尺寸(Unit : mm)							圖形	磁芯參數				單重 (g/set)	Al-value (nH/N ²)											
	A	B	C	D1	D ₂	E	F		C1 (mm ⁻¹)	Le (mm)	Ae (mm ²)	Ve (mm ³)		KP40	KP44	KP44L	KP50	KP95	KP96	KP97	KA50	KA70	KA100	KA120	
EQ45/25.6	45.00±0.70	25.60±0.30	36.00±0.55	35.00±0.70	22.00±0.70	18.00±0.30	9.60±0.30	Fig.1	0.143	57.7	403	23253.10	162.30			16300	15200	20600	19200	19200					
EQ49/28.3	49.00±0.80	28.30±0.30	32.00±0.50	40.00±0.80	28.00min	22.00±0.35	16.30±0.40	Fig.1	0.191	75.3	394	29668.20	153.30			12800	12000	16600	15400	15400					